



SHOWA 8005PF

The SHOWA 8005PF is designed for jobs requiring increased protection without compromising on comfort and tactility. A rolled cuff prevents dirt from entering the glove and allows for easy removal of the glove in case of puncture. The 8005PF is ambidextrous and uses second-skin feel to significantly reduce hand fatigue over long periods of wear.



BENEFITS

- Easy donning and doffing
- Latex-free
- Increased dexterity
- Single-use

FEATURES

- Rolled Cuff
- 100% Nitrile
- Chlorinated
- Ambidextrous
- Powder-free
- Unsupported
- Lightweight

INDUSTRIES



DIY



Municipal Services



Pharmaceutical



Utilities

HAZARDS



Single Use

NORMS & CERTIFICATES



2777

EN ISO 374-1:2016/Type B

JKOPT



EN ISO 374-5:2016

VIRUS



TRADES & APPLICATIONS

- Biotechnology
- Pet Food production
- Washing and cleaning
- Public utility
- Coroner/morgue
- Life sciences
- Pharmaceuticals and API



MATERIAL

Single use

Unsupported



PACKAGING

- Dispenser par case: 20
- Gloves per dispenser: 50
- Gloves per case: 1000

THICKNESS

0.20 mm

LENGTH

240 mm

COATING

Nitrile

LINERS

- Disposable
- Unsupported

SIZES

7/S | 8/M | 9/L | 10/XL

COLOUR

Blue

DISCLAIMER

The descriptions, characteristics, applications and photos are given for information purposes and do not constitute a contractual commitment. The manufacturer reserves the right to make any modifications it deems necessary.

USER INSTRUCTIONS

Gloves provide protection from chemical and mechanical hazards shown. Do not use gloves that show signs of wear. If required, cleanse outer surface of glove with running water. Discard used gloves in compliance with local regulations. Do not wear gloves when there is a risk of entanglement by moving parts of machines.